

MODEL NUMBER 3030C1 PERFORMANCE SPECIFICATION PS3030C1 Accelerometer, Charge Mode REV C, ECN 12932, 09/14/16



- HERMETICALLY SEALED
- ROBUST DESIGN
- LIGHTWEIGHT

| | | ENGLISH | | SI | |
|----------------------------|----------|-----------------|-------|-----------------|------------|
| PHYSICAL | | | | | |
| Weight | | 0.24 | oz | 7.2 | grams |
| Connector [1] | Type | 10-32 | | 10-32 | |
| | Material | 300 Series S.S. | | 300 Series S.S. | |
| Housing | Material | 17-4 PH | | 17-4 PH | |
| Mounting Provision | Stud | 10-32 UNF-2A | | 10-32 UNF-2A | |
| Sensing Element | Material | Ceramic | | Ceramic | |
| | Mode | Compression | | Compression | |
| PERFORMANCE | | | | | |
| Sensitivity, +30%/-10% [2] | | 0.40 | pC/g | 0.04 | pC/m/s^2 |
| Acceleration Range | | [3] | Gpeak | [3] | m/s^2 peak |
| Frequency Range | | [5] to 5000 | Hz | [5] to 5000 | Hz |
| Resonance Frequency | | 30 | kHz | 30 | kHz |
| Linearity [4] | | ±1 | % | ±1 | % |
| Transverse Sensitivity Max | | 5 | % | 5 | % |
| ENVIRONMENTAL | | | | | |
| Shock Max | | 3000 | g pk | 29430 | m/s^2 |
| Vibration Max | | 1000 | g pk | 9810 | m/s^2 |
| Operating Temperature | | -148 to +500 | °F | -100 to +260 | °C |
| Seal | | Hermetic | | Hermetic | |
| ELECTRICAL | | | | | |
| Capacitance, nom | | 126 | pF | 126 | pF |

| his | family | / aiso | ınclı | udes: |
|-----|--------|--------|-------|-------|

| Model | Sensitivity (pC/g) | Range (Gpeak) | Resolution (Grms) | Oper. Temp(°F) |
|-------|--------------------|---------------|-------------------|----------------|
| | | | | |
| | | | | |
| | | | | |
| | | | | |


Please, refer to the performance specifications of the products in this family for detailed description


Supplied Accessories:

1) Accredited Calibration Certificate (ISO 17025)

Notes

- [1] Mates with Dytran cable Model 6013AXX or 6019AXX (XX= Length in feet).
- [2] Measured At 100 Hz, 1 Grms per ISA RP37.2.
- [3] Depends on the gain setting of the charge amplifier used
- [4] Measured using zero-based best straight line method, % of F.S. or any lesser calibrated range.
- [5] Low frequency response is dependent upon the discharge time constant of the charge amplifier. Please, refer to plot below for frequency response for different time constants.





Units on the line drawing are in inches, units in brackets are in millimeters. Refer to 127-3030C1 for more

